




ULTRASUN
RECHARGE YOURSELF

Q6

2024



Product Leaflet

LAMP SPECIFICATIONS

Q6 MAGNUM POWER NON-EU | UV4

| | |
|-----------------------|--|
| Top Lamps | 16 x Sunfit VRX 160W E-Tronic 176 cm |
| Base Lamps | 16 x Sunfit XL 120W E-Tronic 190 cm |
| Facial Lamps | 2 x Sunfit WL 500W High-Pressure |
| Maximum exposure time | 15 minutes |

EU | UV3

| | |
|-----------------------|---|
| Top Lamps | 16 x Sunfit VRX3 120W E-Tronic 176 cm |
| Base Lamps | 16 x Sunfit XL3 120W E-Tronic 190 cm |
| Facial Lamps | 2 x Sunfit WL 500W High-Pressure |
| Maximum exposure time | 20 minutes |

Q6 HIGH POWER NON-EU | UV4

| | |
|-----------------------|--|
| Top Lamps | 16 x Sunfit RXL 120W E-Tronic 190 cm |
| Base Lamps | 16 x Sunfit XL 120W E-Tronic 190 cm |
| Facial Lamps | - |
| Maximum exposure time | 20 minutes |

EU | UV3

| | |
|-----------------------|---|
| Top Lamps | 16 x Sunfit RXL3 120W E-Tronic 190 cm |
| Base Lamps | 16 x Sunfit XL3 120W E-Tronic 190 cm |
| Facial Lamps | - |
| Maximum exposure time | 20 minutes |

TECHNICAL SPECIFICATIONS

Q6 MAGNUM POWER

| | |
|--------------------------|---------------------------------|
| Power supply | 3 x 400V + N + PE 50/60 Hz |
| Plug and cable | 16A CEE 5 x 2,5 mm ² |
| Power | 5.700W |
| Breaker/fuse (slow) | 3 x 16A |
| Minimum net weight | 200 kg |
| Minimum crated weight | 235 kg |
| Boxed dimensions | 227 x 114 x 148 cm |
| Special boxed dimensions | 227 x 114 x 133 cm |

Q6 HIGH POWER

| | |
|--------------------------|---------------------------------|
| Power supply | 3 x 400V + N + PE 50/60 Hz |
| Plug and cable | 16A CEE 5 x 2,5 mm ² |
| Power | 4.100W |
| Breaker/fuse (slow) | 3 x 16A |
| Minimum net weight | 180 kg |
| Minimum crated weight | 215 kg |
| Boxed dimensions | 227 x 114 x 148 cm |
| Special boxed dimensions | 227 x 114 x 133 cm |

AVAILABLE COLORS



**Dream White
Metallic**



**Fancy Red
Metallic**

STANDARD FEATURES



Age
Control



Bluetooth



Body
Cooler



Electronic
Ballasts



IQ Touch
Control



Music Pro



Rainbow
Manager



Voice
Guide



Wellness
Sound

ADDITIONAL FEATURES



PayTronic



DIMENSIONS LxWxH

| | |
|------------|--------------------|
| Open Q6: | 212 x 120 x 147 cm |
| Closed Q6: | 212 x 106 x 123 cm |

* When placing the Ultrason Q6 make sure that the device is surrounded by 10-15 centimetres of free space for air circulation.
* The dimensions indicate an open Ultrason Q6.



+31 (0)74 2912215



info@ultrasuninternational.com



UltrasunInternational.com



Granaatstraat 6
7554 TR Hengelo
The Netherlands